


Shank with welding end

DOUILLE À SOUDER RACOR CON CAÑA PARA SOLDAR

Shank with welding end

MATERIAL MATIÈRE MATERIAL

 **SS** = Stainless steel **Inox**

SIZE DIMENSIONS DIMENSIONES

From DN 13 to 150 mm

■ AL = Aluminium
 ■ BR = Brass **Laiton Latón**
■ ST = Steel **Acier Acero**
■ SS = Stainless steel **Inox**
■ PP = Polypropylene

Trelleborg Fittings 2015

		OD weld. part OD douille OD caña	DN	Ref.	Notes	
 <p>Serrated hose shank. With collar. Douille crantée. A collerette. <i>Acanalado. Con cuello.</i></p>	SS 316	13	13	510 70 00		
		16	16	510 70 08		
		19	19	510 70 01		
		25	25	510 70 02		
		32	32	510 70 03		
		38	38	510 70 04		
		51	51	510 70 05		
		63,5	63	510 70 06		
		76,1	76	510 70 07		
 <p>Serrated hose shank. With collar. Douille crantée. Pour jonc. <i>Acanalado. Con cuello.</i></p>	SS 316		25	25	011 71 96	
			33,7	33,7	510 02 74	
			38	38	011 71 97	
			45	45	510 05 05	
			51	51	011 71 98	
			63,5	63,5	011 71 99	
			70	70	510 04 50	
			76,1	76,1	011 72 00	
			101,5	101,5	011 72 01	
			125	125	510 01 44	
	150	150	011 82 69			
 <p>Serrated hose shank. With collar. Douille lisse. A collerette. <i>Acanalado. Con cuello.</i></p>	SS 316		13	13	510 70 33	
			16	16	510 70 34	
			19	19	510 70 35	
			25	25	510 70 36	
			32	32	510 70 37	
			38	38	510 70 38	
			51	51	510 70 39	
			63,5	63	510 70 40	
			76,1	76	510 70 41	
			104	102	510 70 42	

PAGE 99.
Circlip and ferrule.
Jupe et jonc.
Junta y anillo.